



## MAXGRIP M3 PLUG, YELLOW

PS5965Y | [Pass & Seymour](#)

### FEATURES & BENEFITS

Straight Blade Plug 2pole 3wire 15amp 125v



- Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements; arc resistance exceeds UL requirements.
- Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws; close hinge housing around cord and tighten housing screws.
- Enclosed terminals provide solid, internally-clamped connections.
- Molded finger grips promote safe, sure handling.
- High-visibility yellow and orange, or gray.
- Hospital Grade version displays the Hospital Grade green dot.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Yellow  
Product Series: MaxGrip  
Type: Plug

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: Yes  
cULus: Yes  
cURus: No  
Federal Spec: No  
UL Listing No: Yes  
UN SPSC: 39121402

UR: No

## DIMENSIONS

Height (US): 1.83"

Width (US): 1.34"

## TECHNICAL INFORMATION

Amps: 15A

Volts: 125V

Volts (AC): 125

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

