



## PLUGTAIL® CONNECTORS, RIGHT ANGLE, STRANDED, 6"

PTRA6STR | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

PlugTail® Connectors Right Angle Stranded 6"

For detailed PlugTail® information, visit our [PlugTail Headquarters](#).



- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.
- Available in any wire length up to 25 inches, use Configurable Solutions to order.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

---

### SPECIFICATIONS

#### GENERAL INFO

Product Series: PlugTail

Type: connectors

Special Features: right angle, stranded

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

cULus: Yes

UN SPSC: 39121406

#### DIMENSIONS

Length (US): 6"

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: CHINA

Buy American Act Status: No