



PLUGTAIL® THREE-WAY 15 AMP DECORATOR SWITCH, IVORY

PT26031 | [Pass & Seymour](#)

FEATURES & BENEFITS

PlugTail® Three-Way 15amp 120/277vac Decorator Switch, Ivory

For detailed PlugTail® information, visit our [PlugTail Headquarters](#).

- Ground wire pre-mounted to the box
- Mud ring factory installed
- 4" square x 1 1/2" or 2 1/8" metal boxes
- PlugTail Right Angle Connectors with 12 AWG copper pigtails
- All Double Gang Kits contain two right angle PlugTail connectors
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Product Series: PlugTail

Number Of Poles: 1

Style: Decorator

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 111

CSA Standard: Yes

cULus: Yes

Federal Spec: Yes

UL Listing No: 20

UL Standard: Yes

DIMENSIONS

Depth (US): 1.2"

Height (US): 3.281"

Width (US): 1.6"

TECHNICAL INFORMATION

Amps: 15A

Volts: 120/277VAC
Volts (AC): 120/277

BUY AMERICAN ACT COMPLIANCE

Buy American Act Status: Trade Agreement Act Compliant