
PLUGTAIL® THREE-WAY ILLUMINATED DECORATOR SWITCH 20 AMP, IVORY

PT26261 | [Pass & Seymour](#)



FEATURES & BENEFITS

PlugTail® Three-Way 20amp 120/277vac Illuminated Decorator Switch, Ivory

For detailed PlugTail® information, visit our [PlugTail Headquarters](#).

- Ground wire pre-mounted to the box
- Mud ring factory installed
- 4" square x 1 1/2" or 2 1/8" metal boxes
- PlugTail Right Angle Connectors with 12 AWG copper pigtails
- All Double Gang Kits contain two right angle PlugTail connectors
- This switch is compatible with incandescent loads only and is not recommended for use with LED or CFL lamps.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Product Series: PlugTail
Type: Illuminated
Number Of Poles: 3-way
Style: Decorator

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 111
CSA Standard: Yes
cULus: Yes
Federal Spec: Yes
UL Listing No: 20
UL Standard: Yes

DIMENSIONS

Depth (US): 1.2"
Height (US): 3.281"
Width (US): 1.6"

TECHNICAL INFORMATION

Amps: 15A

Volts: 120/277VAC

Volts (AC): 120/277

BUY AMERICAN ACT COMPLIANCE

Buy American Act Status: Trade Agreement Act Compliant