



## TAMPER-RESISTANT HEAVY-DUTY DECORATOR SPEC GRADE SINGLE RECEPTACLE, BACK & SIDE WIRE, 20A, 125V, GRAY

TR26361GRY | [Pass & Seymour](#)

### FEATURES & BENEFITS

Tamper-Resistant Heavy-Duty Decorator Spec Grade Single Receptacle, Back & Side Wire, 20amp 125volt, Gray

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.



- Dual mechanical shutter system to help prevent insertion of foreign objects.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
- Backed-out tri-drive brass terminal screws for faster installation.
- Internal screw-pressure-plate back and side wire capability.
- Two back wire holes for additional wiring flexibility.
- Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.
- .032 inch thick brass triple-wipe power contacts.
- Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

### SPECIFICATIONS

#### GENERAL INFO

Color: Gray

Type: Single Receptacles

Duty: Heavy Duty

Special Features: Tamper-Resistant,back,side wire

Style: Decorator

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: C22.2 No.42  
CSA Standard: Yes  
Federal Spec: Yes  
UL Listing No: UL498  
UL Standard: Yes  
UN SPSC: 39121406

#### **DIMENSIONS**

Depth (US): 1.188"  
Height (US): 3.281"  
Width (US): 1.322"

#### **TECHNICAL INFORMATION**

Amps: 20A  
Volts: 125V  
Volts (AC): 125  
Capacity: Single  
Grade Type: Federal Specification

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

