



MANUAL CONTROLLER

7843MD | [Pass & Seymour](#)

FEATURES & BENEFITS

Three Pole, Three Phase Switch (7843), Canada Only Motor Disconnect. 40 amps, 600 volts.



- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

SPECIFICATIONS

GENERAL INFO

Number Of Poles: 2

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: C22.23 14
CSA Standard: Yes
UL Listing No: 508
UL Standard: Yes
UN SPSC: 39121507

DIMENSIONS

Depth (US): 1.753"
Height (US): 2.375"
Width (US): 1.825"

TECHNICAL INFORMATION

Amps: 40A
Volts: 600VAC

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

