

STCP

ELECTRONIC THERMOSTAT FOR HEATING FLOORS – MULTIPLE PROGRAMMING

3840 W



DESIGNED FOR:



PROGRAMMING THE COMFORT OF YOUR FEET

This thermostat, specifically designed for heated floor systems, can read floor or ambient temperature. A booklet with more than 250 preset programs is included that can be set by simply pressing the front buttons. The STCP acts like a small computer designed to provide maximum comfort.

252

EASY PROGRAMMING
INCLUDES 252 PRESET PROGRAMS IN “PRE-PROG” MODE

±
1°F

INCREASED SAVINGS AND COMFORT
INCOMPARABLE ACCURACY



ANTICIPATED START
REACH THE TEMPERATURE SETPOINT PRECISELY AT THE PROGRAMMED TIME

7

7-DAY PROGRAMMING



CHOICE OF FLOOR OR AMBIENT TEMPERATURE CONTROL



BACKLIT SCREEN

COLOR

- white

FINISH

- molded plastic

MANUFACTURING

- built-in GFCI and pilot light (test)
- four-wire connection/DPST with bipolar tripping
- 13 ft. floor sensor included*

WATTAGE AND VOLTAGE

- maximum of 1920 W @ 120 V
- maximum of 3330 W @ 208 V
- maximum of 3840 W @ 240 V

CONTROL

- possibility of four events on weekdays and four events on weekends
- anticipated start (the thermostat reaches the desired temperature at the requested time)
- advanced floor or ambient temperature control (your choice)

- protection against power failures (two hours)
- lock option at a maximum temperature setpoint (Security mode)
- display in Celsius or Fahrenheit

ACCURACY

- accurate ambient temperature control of ± 1 °F
- temperature sensing with thermistor

TEMPERATURE RANGE

- Ambient mode: 37 to 95 °F
- Floor mode: 37 to 82 °F

WARRANTY

- three years

* This thermostat is compatible with some floor sensors sold by other manufacturers.

TECHNICAL SPECIFICATIONS

PRODUCT	WATTS	VOLTAGE	AMPERAGE	FREQUENCY	GFCI
CODE	MAXIMUM	VOLTS	AMPERES	HZ	MA
STCPW5*	1920/3330/3840	120/208/240	16	50/60	5

* 5 mA thermostats have an integral Ground-Fault Circuit Interrupter (GFCI) (mandatory in bathrooms and similar room types). Please refer to the electrical and building codes in effect in your region in order to choose the best thermostat to suit your needs. Dimensions: 3 3/8 in. wide, 4 7/8 in. high and 1 in. deep (total depth: 2 3/16 in.)

°STELPRO

Stelpro reserves the right to modify descriptions, manufacturing specifications or prices without prior notice. No returns accepted on optional-color products. For all the latest models and prices, please refer to our website at www.stelpro.com.

