

# 43-in. Full HD LCD Monitor



- Wide-viewing Angle
- 1080p Full HD Resolution
- High-fidelity Digital Signal Processing for Vivid Video
- Fast Response Time (8 ms) with no Image Ghosting
- Built-in Speakers
- 16.7 Million Colors
- Supports HDMI, VGA, and USB Video Input
- Low Energy Consumption for Long Service Life



## Technical Specification

### System

Viewable Picture Area	42.5 in. (measured diagonally)
Aspect Ratio	16:9
Resolution	1920 x 1080 (Full HD)
Backlight	LED
Brightness/Luminance	330 cd/m <sup>2</sup>
Contrast	1200:1
Angle of View	Horizontal: 178° Vertical: 178°
Response Time	8 ms
Display Colors	16.7 Million

### Interface

Video Inputs	<ul style="list-style-type: none"> <li>• One (1) HDMI</li> <li>• One (1) VGA (D-sub)</li> <li>• One (1) USB</li> </ul>
Audio Output	Two (2) Built-in Speakers, 4 W

### Electrical

Power Supply	100 VAC to 240 VAC (±10%), 50/60 Hz
Consumption	Standard: 75 W Standby: ≤ 0.5 W

### Certifications

Electromagnetic Compensation (EMC)	EN 55032:2015(Class A), EN 61000-3-2:2014, EN 61000-3-3:2013, EN 55024:2010+A1:2015, EN 50130-4:2011+A1:2014, EN55035:2017
------------------------------------	--

### Construction/Environmental

Dimensions, without base	969.10 x 566.80 mm x 82.40 mm (38.20 in. x 22.30 in. x 3.20 in.)
Dimensions, packaging	1079.0 mm x 652.0 mm x 129.0 mm (42.48 in. x 25.67 in. 5.08 in.)
Bezel Width	12.80 mm (U/R/L), 22.0 mm (B)
Wall Mount	400.0 mm x 200.0 mm (15.75 in. x 7.87 in.)
Net Weight	7.40 kg (16.30 lb)
Gross Weight	9.50 kg (20.94 lb)
Operating Conditions	0° C to 40° C (32° F to 104° F), 20% to 85% RH

## Ordering Information

Type	Part Number	Description
43 in. Monitor	DHI-LM43-F200	Full HD LCD Monitor
Package Contents	1	Monitor
	1	VGA Cable
	1	Power Cable
	1	Pedestal
	1	Remote Control