

Project Name

Location

Prepared By



NUVO 62-1143R1

2 LT LED LG UP & DOWN SCONCE

Notes

General

| | |
|-------------------|------------|
| Status | Active |
| Finish | White |
| Wattage | 20 |
| Style | Utility |
| CCT (Kelvin) | 3000 |
| Color Temperature | Warm White |
| Length (in.) | 3.16 |
| Width (in.) | 5 |
| Height (in.) | 11.75 |
| Extension (in.) | 4.22 |

Specifications

| | |
|--------------------|-------------------|
| Technology | LED |
| CRI | 90 |
| Lumen Output | 1800 |
| Rated Hours | 50000 |
| Voltage | 120V/277V |
| Dimmable | Non-Dimmable |
| Weight (lb.) | 2.51 |
| Fixture Material | Die Cast Aluminum |
| Recommended Dimmer | N/A |
| Fixture Type | Sconce |

Dimensions

| | |
|-----------------------------------|------|
| Back Plate or Canopy Length (in.) | 4.50 |
| Back Plate or Canopy Width (in.) | 4.50 |

Compliance

| | |
|----------------|--------------------------|
| UL Application | Outdoor |
| Energy Star | Yes |
| ES Unique ID | ESID-2336402 |
| CEC Status | California T24 Compliant |
| CA Prop 65 | Lead |
| RoHS Compliant | Yes |

Additional Information

| | |
|--------------------|--------------------|
| Installation Notes | Mounts Up and Down |
| Warranty | 5 Year Limited |