

Project Name

Location

Prepared By



## NUVO 62-1144R1

2 LT LED LG UP & DOWN SCONCE

Notes

### General

Status	Active
Finish	Black
Wattage	20
Style	Utility
CCT (Kelvin)	3000
Color Temperature	Warm White
Length (in.)	3.16
Width (in.)	5
Height (in.)	11.75
Extension (in.)	4.22

### Specifications

Technology	LED
CRI	90
Lumen Output	1800
Rated Hours	50000
Voltage	120V/277V
Dimmable	Non-Dimmable
Weight (lb.)	2.51
Fixture Material	Die Cast Aluminum
Recommended Dimmer	N/A
Fixture Type	Sconce

### Dimensions

Back Plate or Canopy Length (in.)	4.50
Back Plate or Canopy Width (in.)	4.50

### Compliance

UL Application	Outdoor
Energy Star	Yes
ES Unique ID	ESID-2336402
CEC Status	California T24 Compliant
CA Prop 65	Lead
RoHS Compliant	Yes

### Additional Information

Installation Notes	Mounts Up and Down
Warranty	5 Year Limited