



C Series

The best selling C-Port, the C-Series channel support is designed for superior support of gas and refrigeration piping systems, cable tray, electrical conduit, multiple lines, HVAC equipment and hundreds of other applications. It's available in any length as a roof curb (sleeper) replacement. Maximum Load 750 LBS per Foot.



Available in corrosion resistant stainless steel or aluminum.

Material - Base - 100% recycled rubber, UV resistant

- Strut - 14 gauge galvanized channel strut (13/16" high)

Warranty - 10 years

Recommended Spacing - Refer to local code

May qualify for L.E.E.D. credits

SKU	HEIGHT	WIDTH	LENGTH	WEIGHT	MAX LOAD
C10	47/8" (124mm)	6" (152mm)	9.6" (244mm)	5.30 lbs	750 lbs
C20	47/8" (124mm)	6" (152mm)	19.2" (487mm)	11.23 lbs	1500 lbs
C30	47/8" (124mm)	6" (152mm)	28.8" (731mm)	16.31 lbs	2250 lbs
C40	47/8" (124mm)	6" (152mm)	38.5" (978mm)	21.72 lbs	3000 lbs
C48	47/8" (124mm)	6" (152mm)	48" (1219mm)	27.12 lbs	3750 lbs