



PSG240E

UPC:786685215464

Dimensions:

- **Height:** 4.67 IN
- **Length:** 4.76 IN
- **Width:** 3.35 IN

Weight:2.63 LB

Notes:Ratings for single-phase are at 115V. 0 Hz at DC input.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Special Features:** Varistor transient surge voltage, surge voltage protection against internal surge, safety class 1 with ground connection, finger-safe cover
- **Wattage:** 240W
- **Operating Temperature - Max:** 75 C
- **Operating Temperature - Min:** -20 C
- **Enclosure Material:** Aluminum
- **Frequency Rating:** 47-63 Hz
- **Input Voltage:** 100-240V
- **Output Voltage:** 24V
- **Rated Operational Current:** 2.9A input, 10A output, 15A surge
- **Series:** PSG
- **Terminals:** Heavy-duty screw
- **Phase:** Single-phase
- **Voltage Rating:** 85-264 Vac, 100-375 Vdc

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [PSG240E AutoCAD 2D Footprint \(mm\)](#)

- [PSG240E 2D Drawing Xchange](#)
- [PSG240E 2D PDF](#)
- [PSG240E 3D Inventor](#)
- [PSG240E 3D Model Xchange](#)
- [PSG240E AutoCAD 2D Footprint](#)
- [Installation Instructions for PSG240E Power Supply](#)
- [Eatons PSG Series Power Supplies](#)
- [Eaton Specification Sheet - PSG240E](#)

Certifications:

- CSA Certified
- cULus/UL 60950-1
- UL 508
- EN Listed
- IEC Rated
- cUL Certified

Product compliance:

- RoHS Compliant
- German Safety
- CE Marked