

Models LP3E, LP3M, LP3P, LP3S and LP3T

StreamLine® Low Profile Strobe Light







Model LP3 is offered in five mounting configurations. The LP3S features a three-hole surface mount — ideal for control panels and other flat or flush surfaces. The LP3E features a standard A-19 medium Edison screw-in base. The LP3M features a 1/2" NPT male pipe mount and 18" wire leads. LP3P features an integrated 1/2-inch NPT pipe mount. The "T-mount" LP3T has a popular 2-hole design for wall or flush mounting.

Models LP3M, LP3S and LP3T include a surface gasket to complete the Type 4X installation. An optional dome guard is available for use with the LP3M, LP3S and LP3T when installed flush with a panel. All LP3 units feature a threaded screwon lens to allow for tool free wiring and strobe tube replacement.

Like all StreamLine® products, the LP3 is designed with OEM applications in mind.

- Available in 12-48VDC, 120VAC and 240VAC; LP3E only available in 120VAC
- Edison mount (E), 1/2 "NPT male pipe mount (M), Surface mount (S), T-mount (T), integrated 1/2-inch NPT pipe mount (P)
- Five lens colors: Amber, Blue, Clear, Green and Red
- Screw-on lens provides easy access
- Conformal coated PCB

- Models LP3M, LP3P and LP3S are Type 4X, IP66 enclosure
- IP69K compliant Models LP3E and LP3T are Type 4X, IP66 only
- PLC and triac compatible
- CSA Certified
- UL and cUL Listed

		O P E R A T I N G	FLASH RATE/	LIGHT OUTP	JT
MODEL	VOLTAGE	CURRENT	MINUTE	P E A K ¹	ECP ²
LP3*-012-048 <u>**</u>	12-48VDC	0.44-0.10 amps	80 (+/-15)	175,000 cd	51.5 cd
LP3*-120 <u>**</u>	120VAC	0.10 amps	80 (+/-15)	175,000 cd	51.5 cd
LP3*-240 <u>**</u>	240VAC	0.07 amps	80 (+/-15)	175,000 cd	51.5 cd


^{*} Indicates Mounting Style: (E) Edison A-19 Screw-in Base, (M) Male Pipe Mount, (P) Pipe Mount, (S) Surface Mount, (T) T-Mount

^{**} Indicates color: (A) Amber, (B) Blue, (C) Clear, (G) Green or (R) Red

¹ Peak candela is the maximum light intensity generated by a flashing light during its light pulse

² ECP (Effective Candela) is the intensity that would appear to an observer if the light were burning steadily


StreamLine® Low Profile Strobe Lights (LP3E, LP3M, LP3P, LP3S and LP3T)



Lamp Life:		4,000 Hours
Light Source:		Strobe tube
Operating Temperature:	-31°F to 150°F	-35°C to 66°C
Net Weight: Shipping Weight:	7.3 oz 8.5 oz	0.21 kg 0.24 kg
Diameter: Height:	3.13"	79.5 mm
LP3E	6.06"	153.9 mm
LP3M	5.82"	147.8 mm
LP3P	5.82"	147.8 mm
LP3S	5.02"	127.5 mm
LP3T	5.02"	127.5 mm

Description	Part Number
Lens, Amber	K8589063A
Lens, Blue	K8589063A-01
Lens, Clear	K8589063A-02
Lens, Green	K8589063A-03
Lens, Red	K8589063A-04
Flash Tube Assembly	K149130A
Gasket Kit ¹	K858900353A

¹ Includes gasket for LP3S and LP3T



^{*}LP3E only available in 120VAC

Description Wire Dome Guard for LP3M, LP3S and LP3T

LP3G

Part Number

LP3G