

Eaton rotary disconnect switch

R4H3030FCC

UPC:786685408736

Dimensions:

- **Height:** 4.57 IN
- **Length:** 3.8 IN
- **Width:** 3.3 IN

Weight:1.55 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 30A
- **Fuse Class Provision:** Class CC fuses
- **Number Of Poles:** Three-pole
- **Product Category:** Switch Body
- **Series:** R4
- **Voltage Rating:** 600V

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [R4H3_FCC 3D Inventor](#)
- [R4H3_FCC 3D Model Xchange](#)
- [R4H3_FCC 2D PDF](#)
- [R4H3_FCC 2D Drawing Xchange](#)
- [R4H3_FCC AutoCAD 2D Footprint](#)
- [R4H3_FCC AutoCAD 2D Footprint \(mm\)](#)
- [Eaton Specification Sheet - R4H3030FCC](#)

Certifications:

- IEC Rated
- UL 498
- CSA Certified

Product compliance: No Data



