

Eaton rotary disconnect switch

R4H3030FJ

UPC:786685408750

Dimensions:

- **Height:** 4.57 IN
- **Length:** 4.14 IN
- **Width:** 3.91 IN

Weight:1.55 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 30A
- **Fuse Class Provision:** Class J fuses
- **Number Of Poles:** Three-pole
- **Product Category:** Switch Body
- **Series:** R4
- **Voltage Rating:** 600V

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [R4H3_FJ AutoCAD 2D Footprint \(mm\)](#)
- [R4H3_FJ 2D PDF](#)
- [R4H3_FJ 3D Model Xchange](#)
- [R4H3_FJ 2D Drawing Xchange](#)
- [R4H3_FJ 3D Inventor](#)
- [R4H3_FJ AutoCAD 2D Footprint](#)
- [Eaton Specification Sheet - R4H3030FJ](#)

Certifications:

- IEC Rated
- CSA Certified
- UL 498

Product compliance: No Data



