

## Eaton definite purpose contactor

**C25GNF290A**

**UPC:**782114100165

### **Dimensions:**

- **Height:** 3.75 IN
- **Length:** 3.97 IN
- **Width:** 2.63 IN

**Weight:**2.66 LB

### **Warranties:**

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
- 1 year

### **Specifications:**

- **Accessories:** Mounting plate
- **Connection:** Quick
- **Auxiliary Contact:** Quick connect
- **Coil:** 208/240 Vac, 50/60 Hz
- **Coil Voltage:** 110-120 Vac, 50/60 Hz
- **Enclosure:** Open with metal mounting plate
- **Frame Size:** 15-50A, two- and three-pole
- **Model:** Contactor
- **Number Of Poles:** Three-pole
- **Options:** Individual pkg.
- **Series:** F1
- **Terminals:** Power terminals: Box lugs  
posisetscrew &quick con
- **Type:** Non-reversing

### **Supporting documents:**

- [Eatons Volume 5-Motor Control and Protection](#)
- [C25GNF2 2D PDF](#)
- [C25GNF2 AutoCAD 2D Footprint](#)
- [C25GNF2 2D Drawing Xchange](#)



- [C25GNF2 3D Model Xchange](#)
- [C25GNF2 AutoCAD 2D Footprint \(mm\)](#)
- [C25GNF2 3D Inventor](#)
- [Eaton Specification Sheet - C25GNF290A](#)

**Certifications:**

- UL Listed file E1491 (Guide Number NLDX2)
- CSA Certified
- UL Recognized

**Product compliance:**

- RoHS Compliant
- CE Marked