

2103



MILWAUKEE HEADLAMP

MORE COMPACT. ALL DAY COMFORT. Our Headlamp delivers 350 lumens of TRUEVIEW™ High Definition output in a wide flood beam. The LED headlamp is optimized to be lightweight and compact. The light's strap is made from a washable, sweat absorbing micro-fiber, giving you all-day comfort when worn on the forehead. Built to withstand the toughest conditions, the headlamp light's impact-resistant housing survives drops and is protected from water and dust. You can direct light by pivoting the light head using one of the 7 different tilt positions. You can also get up to 28 hours of runtime with 3 light output modes to manage brightness and runtime. The work headlamp includes four clips for secure attachment to hard hats while you are on the job site. The Milwaukee® Headlamp is covered by our Limited Lifetime warranty.

INCLUDES:

- (1) MILWAUKEE HEADLAMP (2103)
- (2) AAA Batteries

- ✓ 350 Lumens of TRUEVIEW™ High Definition Output
- ✓ IP54: Water and Dust Resistant
- ✓ Optimized for comfort on the head with sweat absorbing micro fiber forehead
- ✓ 2m Impact Rated Housing and IP54: Water and Dust Resistant
- ✓ Includes (4) Clips for Hard Hat Attachment
- ✓ Limited Lifetime Warranty (Excludes Batteries)
- ✓ Washable, Sweat Absorbing Microfiber Strap
- ✓ High Mode: 350 Lumens- 4.0 Hrs., Medium Mode: 150 Lumens- 8.0 Hrs., Low Mode: 25 Lumens- 28 Hrs.
- ✓ Wide Flood Beam Pattern
- ✓ 7-Position Tilting Light Head for Directing Light
- ✓ Powered by (3) AAA Batteries (Included)