

PRODUCT-DETAILS

# 2564SPKIT

## CONNECTOR KIT 1 1/2 FOR 29279



Product image  
not available

### General Information

Extended Product Type	2564SPKIT
Product ID	7TBD105140R0024
EAN	0786209886651
Catalog Description	CONNECTOR KIT 1 1/2 FOR 29279
Long Description	1 1/2 Inch Strain Relief Cord Connector Straight, Liquidtight with Neoprene Bushing For Round, Flexible Cords and Cables

### Ordering

EAN	0786209886651
Customs Tariff Number	7907002000

### Dimensions

Product Net Weight	.82 lb 371.882 g
--------------------	---------------------

### Container Information

Package Level 1 Units	5 piece
Package Level 1 Width	4.5 in 114 mm
Package Level 1 Height	3 in

	76 mm
Package Level 1 Depth / Length	6 in 152 mm
Package Level 2 Units	10 piece
Package Level 2 Width	5.1 in 130 mm
Package Level 2 Height	6.5 in 165 mm
Package Level 2 Depth / Length	10.8 in 274 mm

### Additional Information

Application	Suitable for Use In Hazardous Locations
Brand / Label	T&B
Color	Metallic
Material	Zinc Die Cast
Number of Batteries	0
Product Name	ZINC ELECT CONDUIT FITTING
Product Type	Strain Relief Cord Connectors-Straight
Size	1-1/2 Inch
UPC	786209886651

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	2564SPKIT
Instructions and Manuals	2564SPKIT

### Classifications

ETIM 6	EC000441 - Cable screw gland
ETIM 7	EC000441 - Cable gland
UNSPSC	39121431
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4601 >> Cable gland connector

### Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems



Product image  
not available