

PRODUCT-DETAILS

2454SPKIT

1-1/2IN WATERT CONN .65X1.0-.84X1.2



Product image
not available

General Information

Extended Product Type	2454SPKIT
Product ID	7TBD105140R0021
EAN	0786209998651
Catalog Description	1-1/2IN WATERT CONN .65X1.0-.84X1.2
Long Description	Watertight Connector For Oval Cable, 1-1/2 Inch, Cable Range 0.655 x 1.090 to 0.840 x 1.275 Inch, Die Cast Zinc

Ordering

EAN	0786209998651
Customs Tariff Number	7907002000

Dimensions

Product Net Weight	.74 lb 335.601 g
--------------------	---------------------

Container Information

Package Level 1 Units	5 piece
Package Level 1 Width	4.5 in 114 mm
Package Level 1 Height	3 in

	76 mm
Package Level 1 Depth / Length	6 in 152 mm
Package Level 2 Units	10 piece
Package Level 2 Width	6.2 in 157 mm
Package Level 2 Height	3.5 in 89 mm
Package Level 2 Depth / Length	9.8 in 249 mm

Additional Information

Application	To Connect Underground Feeder Cables to a Box or an Enclosure
Brand / Label	T&B
Color	Metallic
Material	Zinc Die Cast
Number of Batteries	0
Product Name	ZINC ELECT CONDUIT FITTING
Product Type	Watertight Connectors for Oval Cable
Size	1-1/2 Inch
Special Functions	A Design with Two Tapers Inside the Body-A Slow One and a Fast One-Permits the Stocking of Fewer Connectors for Varied Cable Sizes and Allows Maximum Take-Up.
Standards	UL E15170, CSA 589
UPC	786209998651

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	2454SPKIT
Instructions and Manuals	2454SPKIT

Classifications

ETIM 6	EC000441 - Cable screw gland
ETIM 7	EC000441 - Cable gland
UNSPSC	39121431
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4601 >> Cable gland connector

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems



Product image
not available