



# Specification Sheet Ordering Tree

WPX LED				
Series & Lumen Output	Color Temperature	Voltage	Options	Finish
<b>WPX1 LED P1</b> <sup>1</sup> 1,550 Lumens, 11W	<b>30K</b> 3000K	<b>MVOLT</b> 120-277V	<b>(blank)</b> None	<b>DDBXD</b> Dark Bronze
<b>WPX1 LED P2</b> 2,900 Lumens, 24W	<b>40K</b> 4000K	<b>347</b> 347V <sup>3</sup>	<b>E4WH</b> Emergency battery backup, CEC compliant (4W, 0°C min) (available with WPX1 and WPX2) <sup>2</sup>	<b>DWHXD</b> White
<b>WPX2 LED</b> 6,000 Lumens, 47W	<b>50K</b> 5000K		<b>E14WC</b> Emergency battery backup, CEC compliant (14W, -20°C min) (available with WPX1 and WPX2) <sup>2</sup>	<b>DBLBXD</b> Black
<b>WPX3 LED</b> 9,200 Lumens, 69W			<b>PE</b> Photocell for dusk-to-dawn operation <sup>3</sup>	<i>Consult factory for other finish options</i>

Note: The lumen output and input power shown in the ordering tree are average representations of all coinfiguration options. Specific values are available upon request.

1. All WPX wall packs come with 6kV surge protection standard, except WPX1 LED P1 package which comes with 2.5kV surge protection standard. Add SPD6KV option to get WPX1 LED P1 with 6kV surge protection.
2. 347V and PE options not offered with any battery pack options. WPX3 is not available with any battery options.
3. Battery pack options not available with 347V and PE options.

# DLC Listing

- All MVOLT (120V-277V) configurations of WPX wall packs are DLC Premium listed, including:



- Any lumen package (WPX1 P1, WPX1 P2, WPX2, WPX3)
- Any color temperature (3000K, 4000K, 5000K)
- With or without photocell option
- With or without any emergency battery pack options
- Any color finish



- For **347V versions only**, the DLC listing status is shown below:
  - WPX1 (P1 and P2) are not DLC listed
  - WPX2 is DLC Standard
  - WPX3 is not DLC listed



# Stock Product List

Note: All products in stock are MVOLT (120V – 277V) and DDBXD (Dark Bronze)

	Lumen Output	Color Temp	Description	CI Code	UPC Code	Contractor Select?	In Stock?	
							California (WRDC) Illinois (MWDC) Georgia (SEDC)	Texas (SWDC) Pennsylvania (NEDC)
WPX1 P1	1,550	3000K	WPX1 LED P1 30K MVOLT DDBXD	*266CN3	00194994017684	-	Yes	-
		4000K	WPX1 LED P1 40K MVOLT DDBXD	*266CN9	00194994017714	-	Yes	Yes
		5000K	WPX1 LED P1 50K MVOLT DDBXD	*266CNC	00194994017929	-	Yes	Yes
WPX1 P2	2,900	3000K	WPX1 LED P2 30K MVOLT DDBXD	*265SWH	00193048870541	-	Yes	-
		4000K	WPX1 LED P2 40K MVOLT DDBXD	*265SWK	00193048870589	Yes	Yes	Yes
		5000K	WPX1 LED P2 50K MVOLT DDBXD	*265SWM	00193048870572	Yes	Yes	Yes
WPX2	6,000	3000K	WPX2 LED 30K MVOLT DDBXD	*265SX2	00193048870725		Yes	-
		4000K	WPX2 LED 40K MVOLT DDBXD	*265SX3	00193048870756	Yes	Yes	Yes
		5000K	WPX2 LED 50K MVOLT DDBXD	*265SX6	00193048870770	Yes	Yes	Yes
WPX3	9,200	3000K	WPX3 LED 30K MVOLT DDBXD	*265SX8	00193048870800	-	Yes	-
		4000K	WPX3 LED 40K MVOLT DDBXD	*265SX9	00193048870794	-	Yes	Yes
		5000K	WPX3 LED 50K MVOLT DDBXD	*265SXC	00193048870824	-	Yes	Yes