

Project Name

Location

Prepared By



**Notes**

[www] 09-31-2020 01:09:34

**General**

Status	Discontinued
Substitute	S39750
Watts	30
Incandescent Equivalent	200
Fluorescent Equivalent	55
HID Equivalent	150
Volts	100V-277V
Shape	Corncob
Base	Medium
ANSI Base	E26
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	83
Lumens	3900
Beam Spread	360
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	Corncob
Technology	LED
Min Compartment Size	Length: 11 in. Width: 8 in. Depth: 8 in.
Ballasting Requirements	Direct wire range voltage 100-277V

**Electrical**

Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +65C (+149F)

**Physical**

MOL	6.38
MOD	3.19
Housing Color	White

**Additional Information**

Additional Info	Width 360 deg 3.2 in.; Width 270 deg 6.8 in.; Width 180 deg 7.7 in.
Enclosure Rating	Enclosed Rated Lamp
Rated For Enclosed Fixture	Yes
IP Rating	IP65
Warranty	5 Year Limited - Hi-Pro

**Compliance**

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
CEC Status	Lawful for sale in California
RoHS Compliant	Yes
SDS Sheet	LED_Lamp

