

# OHB125J10B



## General Information

<b>Extended Product Type:</b>	OHB125J10B
<b>Product ID:</b>	1SCA127770R1001
<b>EAN:</b>	6417019576855
<b>Catalog Description:</b>	OHB125J10B HANDLE
<b>Long Description:</b>	PISTOL HANDLE, BLACK FOR 10MM SHAFT

## Additional Information

<b>Color:</b>	Black
<b>Country of Origin:</b>	Finland (FI)
<b>Customs Tariff Number:</b>	85389099
<b>Degree of Protection:</b>	IP65
<b>EAN:</b>	6417019576855
<b>ETIM 5:</b>	EC000229 - Handle for power circuit breaker
<b>ETIM 6:</b>	EC000229 - Handle for power circuit breaker
<b>Handle Length:</b>	125 mm
<b>Handle Type:</b>	Pistol
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Industrial IT Certification Level:</b>	0
<b>Invoice Description:</b>	OHB125J10B HANDLE
<b>Minimum Order Quantity:</b>	1 piece
<b>Object Classification Code:</b>	N/A
<b>Order Multiple:</b>	1 piece
<b>Package Level 1 EAN:</b>	6417019576855
<b>Package Level 1 Gross Weight:</b>	0.16 kg
<b>Package Level 1 Height:</b>	50 mm
<b>Package Level 1 Length:</b>	125 mm
<b>Package Level 1 Units:</b>	1 piece
<b>Package Level 1 Width:</b>	70 mm
<b>Product Main Type:</b>	OHB125
<b>Product Name:</b>	Handle
<b>Product Net Depth:</b>	45 mm
<b>Product Net Height:</b>	66 mm
<b>Product Net Length:</b>	125 mm
<b>Product Net Weight:</b>	0.16 kg
<b>Product Type:</b>	OHB
<b>Selling Unit of Measure:</b>	piece
<b>Short Description:</b>	HANDLE
<b>Special Functions:</b>	J10B
<b>Suitable for Product Class:</b>	MCCB