

## Safety Switch Body

LS-S20A

UPC:786685392509

### Dimensions:

- **Height:** 1.32 IN
- **Length:** 2.99 IN
- **Width:** 1.22 IN

### Warranties:

- 1 year

### Specifications:

- **Accuracy:** Plus or minus 0.02mm
- **Connection:** Screw Terminals
- **Contact Rating:** 6A at 230 Vac, 3A at 24 Vdc
- **Output:** 2NO with slow make/break
- **Contact Configuration:** 2NC with positive opening contacts
- **Enclosure Material:** Plastic
- **Environmental Rating:** IP66, IP67
- **Maximum Ac Current:** 6A at 230 Vac
- **Maximum Dc Current:** 3A at 24 Vdc
- **Operating Speed:** 99.97 cm/sec
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Series:** LS-Titan

### Supporting documents:

- [LS-Titan Safety Limit Switches](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - LS-S20A](#)

**Certifications:** No Data

**Product compliance:** No Data

