

Model FB2LED Fireball® LED Warning Light



Model FB2LED is a multi-pattern LED available in five colors and features Federal Signal's patented Power Select[™] technology. Power Select[™] allows a user to select one of three flash patterns: 60 FPM (default), 120 FPM or steady. FB2LED features Federal Signal's patented Power Select[™] Technology which allows a user to change between flash patterns without having to open the unit, by following a sequence when power is applied.

FB2LED is available in 12-24VDC and 120-240VAC. The zinc die-cast alloy base features an integrated 1/2-inch NPT pipe mount and three holes required for surface mount configurations.


The housing for FB2LED is designed to protect against corrosion, vibration, and water- and dust-ingress and high pressure and temperature spray-downs. The unit is ideal in harsh applications including industrial warning, process control, status indication, and food processing.

EATURES

- Available in 12-24VDC or 120-240VAC
- Five lens colors: Amber, Blue, Clear, Green, and Red
- 50,000 hour LED
- Patented Power Select[™] technology
- Three flash pattern options: 60 FPM (default), 120 FPM, or steady
- Integrated 1/2-inch NPT pipe and surface mount
- Indoor/outdoor use
- Conformal coated PCBA
- Type 4X, IP66 enclosure
- IP69K compliant
- UL and cUL Listed

MODEL	V O L T A G E	O P E R A T I N G C U R R E N T	L	MOUNT
FB2LED-012-024 *	12-24VDC	0.48-0.24 amps	300 cd	1/2 " NPT Pipe/Surface
FB2LED-120-240 *	120-240VAC 50/60Hz	0.03 amps	300 cd	1/2 " NPT Pipe/Surface


* Indicates color: (A) Amber, (B) Blue, (C) Clear, (G) Green, or (R) Red



S P E C I F I C A T I O N S

Lamp Life:		50,000 Hours
Light Source:		LED
Operating Temperature:	-49°F to 150°F	-45°C to 66°C
Net Weight: Shipping Weight:	1.5 lbs 1.8 lbs	0.68 kg 0.82 kg
Height: Diameter:	5.25" 4.10"	133.4 mm 104.1 mm

HOW TO ORDER



REPLACEMENT PARTS

Description	Part Number
PCBA, 12-24VDC, for Amber, Green, or Red units	K20000401A
PCBA, 12-24VDC, for Blue or Clear units	K20000401A-01
PCBA, 120-240VAC, for Amber, Green, or Red units	K20000426A
PCBA, 120-240VAC, for Blue or Clear units	K20000426A-01

OPTIONAL ACCESSORIES

Description	Part Number
Wire Guard	FB2G
Wall Mount Bracket, 4X Rated	LSWB
Corner Mount Bracket, 3R Rated	LCMB2*

* LCMB2 is 3R Rated. In combination with a 4X unit, the product defaults to 3R.

