

WIRE ARMOUR™

PROFESSIONAL ELECTRICAL TAPE

When performance matters, count on WireArmour™ Electrical Tape from IDEAL Electrical to get the job done.



Premium Professional

Colour-Coding | Heavy Duty | Contractor Pro

General Purpose

Black | Colour-Coding

Special Use Tapes

Linerless Rubber Tape | Mastic Pads
Rubber Mastic Tape | Corrosion Tape

THE ELECTRICIAN'S
CHAMPION™



Vinyl Electrical Tape

Premium Professional

- Primary insulation up to 600V and 105°C
- Cold and weather resistant
- Great elasticity
- Flame retardant
- Great resistance to sun, water, oil, acids, alkalis and corrosive chemicals
- Multiple colors available for marking and identification of phases
- Highly UV resistant



	Part No.	Color	Size	Case Qty.	UPC Code
PREMIUM PROFESSIONAL	46-33	Black	3/4" x .007" x 66'	10	783250799022
	46-88	Black	3/4" x .0085" x 66'		783250796076
	46-35-WHT	White	3/4" x .007" x 66'		783250796007
	46-35-BLU	Blue			783250795987
	46-35-RED	Red			783250795994
	46-35-GRN	Green			783250796014
	46-35-YLW	Yellow			783250796021
	46-35-ORN	Orange			783250796038
	46-35-BRN	Brown			783250796045
	46-35-GRY	Gray			783250796052
46-35-VIO	Violet	783250796069			
Contractor Pro	46-PRO	Black	3/4" x .007" x 66'	10	783250809691



General Purpose

- Primary insulation up to 600V and 80°C
- Good elasticity
- Flame retardant
- Affordable solution
- Available in multiple colors for wire marking and identification



	Part No.	Color	Size	Case Qty.	UPC Code
GENERAL PURPOSE	46-1700	Black	3/4" x .007" x 60'	10	783250795963
	46-1700C-WHT	White	3/4" x .007" x 66'		783250809950
	46-1700C-BLU	Blue			783250809899
	46-1700C-RED	Red			783250809943
	46-1700C-GRN	Green			783250809912
	46-1700C-YLW	Yellow			783250809967
	46-1700C-ORN	Orange			783250809936
	46-1700C-BRN	Brown			783250809905
	46-1700C-GRY	Gray			783250809929
	46-1700C-VIO	Violet			783250809974

WIRE ARMOUR™

Special Use Tape

Linerless Rubber Tape

- Primary insulation up to 69kV
- Linerless ethylene rubber
- Excellent conformability to complex shapes
- Moisture, corrosion, and chemical resistant
- High thermal conductivity allowing heat to dissipate from joint
- Overload temperature: 266°F
- Elongation: 890%



Part No.	Dimensions	UPC Code
46-130C-3/4x30	3/4" x 0.03" x 30'	783250809844
46-130C-1x30	1" x 0.03" x 30'	783250809875
46-130C-1-1.5x30	1-1/2" x 0.03" x 30'	783250809851
46-130C-2x30	2" x 0.03" x 30'	783250809868

Rubber Mastic Tape

- Primary insulation up to 2kV
- Insulating and moisture sealing splices and terminations
- Moisture, corrosion and chemical resistant
- Suitable for direct burial and overhead applications
- Overload Temperature: 266°F
- Elongation: 890%



Part No.	Dimensions	UPC
46-2228-1x10	1" x 0.065" x 10'	783250809882

Mastic Pads

- Primary insulation up to 1kV
- Superior adhesion and dielectric strength
- Sealing and insulating for buried, submerged overhead electrical connections
- Resistant to UV rays and impermeable to ozone, water, soil, dirt and corrosive chemicals
- Overload temperature: 266°F
- Package of 10



Part No.	Dimensions	UPC
46-2200-6.5x4	6-1/2" x 0.13" x 4"	783250810284

Corrosion Tape

- Protects pipe, joints, conduit and couplings in overhead or direct burial applications
- Highly resistant to sun, water, oil, acids, alkalis and corrosive chemicals
- Bacteria and fungus resistant
- Pressure sensitive
- Thickness: 10mil



Part No.	Dimensions	UPC Code
46-50-UNPRINT-2	2" x 0.01" x 100'	783250809981

PROFESSIONAL ELECTRICAL TAPES