## SATCO NUVO

Project Name

Location

Prepared By



## **SATCO S39752**

60W/LED/HID/MB-G3/50K/100-277V

Notes

General	
Status	Active
Watts	60
Incandescent Equivalent	500
Fluorescent Equivalent	85
HID Equivalent	250
Volts	100V-277V
Shape	Corncob
Base	Mogul Extended
ANSI Base	EX39
Finish	Clear
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	80
Lumens	8400
Beam Spread	120;150;260
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	LED HID
Technology	LED
Min Compartment Size	Width: 9.30 in. Depth: 9.30 in Height: 9.80 in.
Electrical	
Operating Frequency	50/60 Hz
Power Factor	>0.9
Surge Protection	Built-in surge protection - 4KV

Electrical		
Operating Frequency	50/60 Hz	
Power Factor	>0.9	
Surge Protection	Built-in surge protection - 4KV	
THD	<20%	
Operating Temperature	-20C (-4F) to a maximum of +65C (+149F)	

Physical		
MOL	7.76	
MOD	4.13	
Housing Color	White	
Photocell	Optional Add-On	
Weight (lb.)	2.05	

Additional Information		
Additional Info	PIR Sensor available as an accessory	
Rated For Enclosed Fixture	Yes	
IP Rating	IP64	
Specification Note	Closed 260 deg; Partial 150 deg; Open 120 deg	
Warranty	5 Year Limited - Hi-Pro	

Compliance	
Safety Listing	cULus Classified
Location Rating	Damp
Energy Star	No

For More Information Visit: https://www.satco.com/









	DLC Approved	Yes
	DLC ID	PL1DH99JBHHE
	California Status	Lawful for sale in California
	Nevada Status	Lawful for sale in Nevada
	RoHS Compliant	Yes
	SDS Sheet	LED_Lamp







