



### Overview

Lead time	Usually in Stock
-----------	------------------

### General

Provided equipment	CD with software User Manual
--------------------	---------------------------------

### Physical

Color	Black
Maximum Depth	4.49 in (11.4 cm)
Maximum Height	1.50 in (3.8 cm)
Net Weight	0.18 lb(US) (0.08 kg)
Maximum Width	4.76 in (12.1 cm)

### Conformance

Standards	EN 55022 Class A EN 55024 FCC Part 15 class A ICES-003
Product certifications	AS/NZS 3548 (C-Tick) Class A GOST VCCI Class A

### Environmental

Ambient air temperature for operation	32...113 °F (0...45 °C)
Operating altitude	0...10000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	23...113 °F (-5...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Communications & Management

Authentication	Radius
Communication network type	RJ-45 10/100 Base-T
Communication port protocol	HTTP HTTPS IPv4 IPv6 NTP SMTP SNMP v1 SNMP v2c SNMP v3 SSH v1 SSH v2 SSL TCP/IP Telnet

## Ordering and shipping details

Category	09305 - INDUSTRIAL UPS
GTIN	00731304267416
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	IN

## Packing Units

Package 1 Height	2.01 in (5.1 cm)
Package 1 width	9.25 in (23.5 cm)
Package 1 Length	6.26 in (15.9 cm)

## Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Halogen content performance	Halogen free product

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------