

Catalog No. 1SAJ929200R0020

Description: CEM11-FBP.20 Earth Leakage Monitor 20 mm Ø, setting 80 mA ... 1.7 A

UPC No 4013614383533

Home > Electronic Relays & Controls > UMC

CEM11-FBP.20 Earth Leakage Monitor 20mm



Representative Image

Descriptors

Category	UMC
----------	-----

Specifications

Product Name	Earth Leakage Monitor
Rated Control Supply Voltage	24 V DC
Ambient Air Temperature	Storage -40 ... +75 degree Celsius Operation 0 ... +60 degree Celsius
RoHS Status	Following EU Directive 2011/65/EU

Dimensions

Product Net Width	76 mm
Product Net Height	31 mm
Product Net Depth / Length	56 mm
Product Net Weight	117 gram

Package Information

Package Level 1 Units	1 piece
Package Level 1 Width	76 mm
Package Level 1 Height	31 mm
Package Level 1 Depth / Length	56 mm
Package Level 1 Gross Weight	0.117 kg
Package Level 1 EAN	4013614383533

Ordering

Minimum Order Quantity	1
Customs Tariff Number	85043129
ECCN	N
ECN	N