



Representative Image

Catalog No. 1SVR405612R7100

Description: CR-M110AC3L Pluggable interface relay 3c/o, A1-A2=110VAC, 250V/10A, LED

UPC No 4013614497629

Home > Electronic Relays & Controls > Interface Relays & Optocouplers

Descriptors

Category	Interface Relays & Optocouplers
----------	---------------------------------

Specifications

Function	Pluggable miniature interface relay CR-M
Rated Control Supply Voltage	110 V AC
Output Signal	250 V / 10 A
Output	3 c/o (SPDT) contacts
Contact material	silver-nickel alloy (AgNi)
Product Main Type	CR-M
Sub-Function	Relay with built in LED
RoHS Status	Following EU Directive 2011/65/EU
Object Classification Code	K

Classifications

ETIM 4	EC001437 - Switching relay
ETIM 5.0	EC001437 - Switching relay
ETIM 6.0	EC001437 - Switching relay
ETIM 7	EC001437 - Switching relay
eClass	7.0 27371601

Dimensions

Product Net Width	21.2 mm
Product Net Height	35.6 mm
Product Net Depth / Length	27.5 mm
Product Net Weight	0.033 kg

Package Information

Package Level 1 Units	10 piece
Package Level 1 Width	114 mm

Package Information

Package Level 1 Height	61 mm
Package Level 1 Depth / Length	50 mm
Package Level 1 Gross Weight	0.35 kg
Package Level 1 EAN	4013614373442

Ordering

Minimum Order Quantity	10
Customs Tariff Number	85364900
ECCN	N
ECN	N
ABB MDF Code	3DL - Relays (LV / Control + Protection)
ABB Business Unit	ELSP - Smart Power