



Representative Image

Alternate Catalog No. SU202M-C0.5
Catalog No. 2CDS272337R0984

Description: UL489 MCB 2P C 0.5A 480/277

UPC No 4016779930970

Home > Circuit Breakers > Miniature Circuit Breakers > UL 489 Branch Circuit MCBs

SU202M-C0,5 Miniature Circuit Breaker C-Char., 10kA, 0,5A, 2P UL489

Descriptors

Category	UL 489 Branch Circuit MCBs
----------	----------------------------

Specifications

Number of Poles	2
Tripping Characteristic	C
Rated Current	0.50 A
Standards	CSA 22.2 No. 5 IEC/EN 60947-2 UL 489
Product Main Type	SU200M
Rated Voltage (V)	(480Y / 277 V AC) (96 V DC)
Interrupting Rating acc. to UL489	(480Y / 277 V AC) 10 kA (96 V DC) 10 kA
Rated Ultimate Short-Circuit Breaking Capacity	(400 V AC) 15 kA
Power Loss	2,8 W at Rated Operating Conditions per Pole 1,4 W