



## Legrand

Hospital-Grade USB Charger with Tamper-Resistant 20A Duplex Receptacles, White

Part No. TR8300HUSBW



Designed for the healthcare market and capable of withstanding heavy use due to its UL Hospital Grade certification. Features include an improved overall 3.1A USB charging capability, auto-ground clips, zinc-plated ground terminal screw, as well as triple-wipe brass contacts for lasting retention. The screw-pressure-plate back wiring makes installation fast and easy. Also available in black, green, gray, ivory, light almond, nickel, red and white. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

### Features & Benefits

Overall 3.1A USB charging capability: Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices

AC receptacles available in 15 and 20 Amp, 125V

AC receptacles are tamper-resistant as standard: patented shutter system prevents improper insertion of foreign objects.

Multiple color options available.

Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire.

Stainless steel auto-ground clips assure positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### Specifications

#### General Info

Color White

UPC Number 785007031560

Countries Of Origin China

Product Line Pass & Seymour

#### Listing Agencies / 3rd Party Agencies

cULus Listed Yes

#### Additional Information

Product Environmental Profile Yes