



Legrand

Fed Spec Grade USB Charger w/ Tamper-Resistant 15A Duplex Receptacles,
Ivory
Part No. TR5262USB1



Designed for commercial markets with strength and durability in mind, this combination USB charger duplex receptacle features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Overall 3.1A USB charging capability: Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.

AC receptacles are tamper-resistant as standard: patented shutter system prevents improper insertion of foreign objects.

Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire.

For covering patents, see www.legrand.us/patents.

AC receptacles available in 15 and 20A, 125V.

Multiple color options available.

Stainless steel auto-ground clips assure positive ground.

Specifications

General Info

Color Ivory

UPC Number 785007031775

Countries Of Origin China

Product Line Pass & Seymour

Application Sector Commercial

Standard CSA Listed, cULus, FSUL, UL Listed, RoHS

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Additional Information

Product Environmental Profile Yes

Technical Information

Number of Poles Double Pole

Voltage 125 V

Connection Side & Back Wired

Dielectric Strength	Withstands 2000V minimum
Phase	Single
Temperature Rating	Maximum continuous +60°C, minimum -40° without impact
Wire Size	#14 - #10 AWG Copper Conductor Only
Number of Wires	3
Environmental Conditions	UL94 V2
