



## Legrand

Fed Spec Grade USB Charger w/ Tamper-Resistant 15A Duplex Receptacles,  
Brown  
Part No. TR5262USB



Designed for commercial markets with strength and durability in mind, this combination USB charger duplex receptacle features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

### Features & Benefits

Overall 3.1A USB charging capability: Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.

AC receptacles are tamper-resistant as standard: patented shutter system prevents improper insertion of foreign objects.

Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

AC receptacles available in 15 and 20A, 125V.

Multiple color options available.

Stainless steel auto-ground clips assure positive ground.

### Specifications

#### General Info

Color Brown

UPC Number 785007031782

Countries Of Origin China

Product Line Pass & Seymour

Application Sector Commercial

Standard CSA Listed, cULus, FSUL, UL Listed, RoHS

#### Listing Agencies / 3rd Party Agencies

cULus Listed Yes

#### Additional Information

Product Environmental Profile Yes

#### Technical Information

Number of Poles Double Pole

---

<b>Voltage</b>	125 V
<b>Connection</b>	Side & Back Wired
<b>Dielectric Strength</b>	Withstands 2000V minimum
<b>Phase</b>	Single
<b>Temperature Rating</b>	Maximum continuous +60°C, minimum -40° without impact
<b>Wire Size</b>	#14 - #10 AWG Copper Conductor Only
<b>Number of Wires</b>	3
<b>Environmental Conditions</b>	UL94 V2

---