

## Reduced voltage motor solid state starters

**S611F414N3S**

**UPC:**786685480398

### Dimensions:

- **Height:** 9.5 IN
- **Length:** 29.69 IN
- **Width:** 17.56 IN

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Amperage Rating:** 414A
- **Frame Size:** F-frame
- **Max Hp Rating:** 150 hp at 208V, 150 hp at 240V, 350 hp at 480V, 450 hp at 600V
- **Phase:** Three-phase
- **Type:** Standard

### Supporting documents:

- [Eatons Volume 6-Solid-State Motor Control](#)
- [S611F AutoCAD 2D Footprint \(mm\)](#)
- [S611 Frame E/F Soft Starter](#)
- [S611F 3D Model Xchange](#)
- [S611F 2D Drawing Xchange](#)
- [S611F AutoCAD 2D Footprint](#)
- [S611 Soft Starter Quick Start Installation Guide](#)
- [S611 Soft Starters](#)
- [Eaton Specification Sheet - S611F414N3S](#)

### Certifications:

- IEC 60947-2
- CSA Std. C22.2 No.235
- UL 1077



**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.