

**Alternate Catalog No. SU203M-C25**  
**Catalog No. 2CDS273337R0254**

**Description: UL489 MCB 3P C 25A 480/277**

**UPC No 4016779931359**

**Home > Circuit Breakers > Miniature Circuit Breakers > UL 489 Branch Circuit MCBs**

SU203M-C25 Miniature Circuit Breaker C-Char., 10kA, 25A, 3P UL489



**Descriptors**

Category	UL 489 Branch Circuit MCBs
----------	----------------------------

**Specifications**

Number of Poles	3
Tripping Characteristic	C
Rated Current	25 A
Standards	CSA 22.2 No. 5 IEC/EN 60947-2 UL 489
Product Main Type	SU200M
Rated Voltage (V)	(480Y / 277 V AC) (96 V DC)
Interrupting Rating acc. to UL489	(480Y / 277 V AC) 10 kA (96 V DC) 10 kA
Rated Ultimate Short-Circuit Breaking Capacity	(400 V AC) 15 kA
Power Loss	9,6 W at Rated Operating Conditions per Pole 3,2 W