



Representative Image

Alternate Catalog No. EOT45U3P3-S Catalog No. 1SCA103984R1001

Description: UL508 3P 60A NF N3R BK SEL HDL

UPC No 6417019383323

Home > Switches & Disconnects > Disconnect & Safety Switches > Enclosed Rotary Disconnects

Enclosed Switch Disconnecter, 3-p. Max. Horse power rating at three phase 480V 30HP. General purpose current rating 60A. Plastic enclosure, NEMA Type 3R Rainproof, 12 Indoor, Selector handle. Interlocked cover. Defeatable interlocking.

Descriptors

Category	Enclosed Rotary Disconnects
----------	-----------------------------

Specifications

Standards	IEC 60947-1, -3 / UL 508
Number of Poles	3
Ampere Rating UL/CSA	60 A
Enclosure Type	NEMA Type 3R Rainproof, 12 Indoor
Enclosure Material	Non-Metallic
Handle Type	Selector handle
Handle Color	Black
Mounted Auxiliary Contacts	0 NO, 0 NC