

Alternate Catalog No. SU202M-K30
Catalog No. 2CDS272337R0527

Description: UL489 MCB 2P K 30A 480/277

UPC No 4016779932776

Home > Circuit Breakers > Miniature Circuit Breakers > UL 489 Branch Circuit MCBs

SU202M-K30 Miniature Circuit Breaker K-Char., 10kA, 30A, 2P UL489



Representative Image

Descriptors

| | |
|----------|----------------------------|
| Category | UL 489 Branch Circuit MCBs |
|----------|----------------------------|

Specifications

| | |
|--|---|
| Number of Poles | 2 |
| Tripping Characteristic | K |
| Rated Current | 30 A |
| Standards | CSA 22.2 No. 5 IEC/EN 60947-2 UL 489 |
| Product Main Type | SU200M |
| Rated Voltage (V) | (480Y / 277 V AC) (96 V DC) |
| Interrupting Rating acc. to UL489 | (480Y / 277 V AC) 10 kA (96 V DC) 10 kA |
| Rated Ultimate Short-Circuit Breaking Capacity | (400 V AC) 15 kA |
| Power Loss | 7 W at Rated Operating Conditions per Pole 3,5 W |