



**Alternate Catalog No. SU203M-K20**  
**Catalog No. 2CDS273337R0487**

**Description: UL489 MCB 3P K 20A 480/277**

**UPC No 4016779930390**

**Home > Circuit Breakers > Miniature Circuit Breakers > UL 489 Branch Circuit MCBs**

SU203M-K20 Miniature Circuit Breaker K-Char., 10kA, 20A, 3P UL489

**Descriptors**

|          |                            |
|----------|----------------------------|
| Category | UL 489 Branch Circuit MCBs |
|----------|----------------------------|

**Specifications**

|  |   |
|--|---|
| Number of Poles                                | 3   |
| Tripping Characteristic                        | K   |
| Rated Current                                  | 20 A  |
| Standards                                      | CSA 22.2 No. 5<br>IEC/EN 60947-2<br>UL 489            |
| Product Main Type                              | SU200M  |
| Rated Voltage (V)                              | (480Y / 277 V AC)<br>(96 V DC)                        |
| Interrupting Rating acc. to UL489              | (480Y / 277 V AC) 10 kA<br>(96 V DC) 10 kA            |
| Rated Ultimate Short-Circuit Breaking Capacity | (400 V AC) 15 kA                                      |
| Power Loss                                     | 7,5 W<br>at Rated Operating Conditions per Pole 2,5 W |