

Eaton, 22.5 mm RMQ-Titan Pushbutton

M22-D-G-K10

UPC:786685276267

Dimensions:

- **Height:** 2.16 IN
- **Length:** 1.46 IN
- **Width:** 1.18 IN

Weight:.085 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Pushbutton
- **Action:** Momentary
- **Actuator:** Button, Flush
- **Actuator Color:** Green
- **Bezel:** Silver
- **Contact Configuration:** 1NO
- **Enclosure:** IP67, IP69K
- **Environmental Rating:** IP67, IP69K, NEMA 4X, 13
- **Illumination:** Non-illuminated
- **Mounting:** Flush
- **Nema Rating:** NEMA 4X, 13
- **Operating Cycles:** 5,000,000 operations
- **Size:** 22.5 mm
- **Product Category:** Flush pushbutton
- **Series:** M22

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [M22 Operators and Accessories](#)



- [M22 Pilot Devices](#)
- [Eaton Specification Sheet - M22-D-G-K10](#)

Certifications:

- CSA Certified
- CCC Marked
- Lloyd's Register Certified

Product compliance:

- CE Marked
- GoST-R
- Bureau Veritas