



CANADIAN WIRETWIST™ CONNECTORS



- Heavy gauge outer shell for superior dielectric performance
- Heat-set, square-cut springs stay in place, and firmly grip wire
- CSA Certified and UL Listed for 600V maximum building wire, and 1000V maximum for signage/fixture applications

Wire size range (solid and/or stranded):

- **C3** - 18 to 14 AWG (min. 1x14 + 2x18 / max. 1x10 + 2x14)
- **C4** - 18 to 10 AWG (min. 2x18 / max. 3x14)
- **C6** - 18 to 10 AWG (min. 2x16 + 2x18 / max. 3x10)

CSA 22.2 #188 Certified



CU/CU ONLY

PACKAGE DETAILS / CAT #	C3	C4	C6
C-Pak of 100 Connectors	30-0C3	30-0C4	30-0C6
Flip Tub of 500 Connectors	30-3C3	30-3C4	30-3C6
Flip Tub of 1,000 Connectors	30-4C3	30-4C4	-
Barrel of Connectors	30-6C3 (45K Pieces)	30-8C4 (25K Pieces)	30-8C6 (20K Pieces)

WIRETWIST™ CU/AL CONNECTORS



Copper to aluminum connectors

- The only copper to aluminum twist-on connector specifically designed to provide a secure connection while preventing aluminum corrosion
- Pre-filled antioxidant compound prevents oxidation of aluminum conductors
- Swept wings and hexagonal head for easy installation by hand or with standard nut driver
- Live-action, square-wire spring expands and contracts with aluminum wire
- CSA C22.2 #188 Certified

PACKAGE DETAILS	CAT #
Card of 15 Connectors	30-1CCUAL
Jar of 75 Connectors	30-2CCUAL
Jar of 300 Connectors	30-3CCUAL

CONNECTORS