



MSC40 Series

200 AMP - MULTI POSITION STUD TYPE 400 Amp Main c/w Blank Compartment

CATALOGUE #	TYPE	DESCRIPTION	DIMENSIONS (IN.)			WEIGHT
			H	W	D	
MSC42TW	U/G	2 gang, c/w 1/2" Compression studs	22 ¹³ / ₁₆	27 ¹³ / ₁₆	6 ¹ / ₈	48 lbs.
MSC43TW	U/G	3 gang, c/w 1/2" Compression studs	22 ¹³ / ₁₆	37 ¹ / ₁₆	6 ¹ / ₈	65 lbs.
MSC44TW	U/G	4 gang, c/w 1/2" Compression studs	22 ¹³ / ₁₆	46 ⁵ / ₁₆	6 ¹ / ₈	83 lbs.
MSC45TW	U/G	5 gang, c/w 1/2" Compression studs	22 ¹³ / ₁₆	55 ⁹ / ₁₆	6 ¹ / ₈	103 lbs.
MSC46TW	U/G	6 gang, c/w 1/2" Compression studs	22 ¹³ / ₁₆	64 ¹³ / ₁₆	6 ¹ / ₈	121 lbs.

* Also available with two (2) blank compartments (see MSC800 Series)

- Factory Bussed 400 Amp Mains
- 200 Amp, 600 VOLT per position
- 2 - 6 position horizontal
- 4 Jaw meter sockets
- CSA weatherproof enclosure 3R
- Approved conductor range:
Line - studs (1/2" per phase) provided for compression type wire connectors
Load - #6 - 250 MCM CU/AL
- Underground only

- Use **SXK503** for 5th jaw at 9 O'clock
- Add suffix "H" for right hand entry

KNOCKOUT CODE	CONDUIT SIZE
G	1 ¹ / ₄ ", 1 ¹ / ₂ ", 2", 2 ¹ / ₂ "
S	3", 3 ¹ / ₂ ", 4"
AA	1/2"

