

# MSC20 Series



METER  
SOCKETS

## 200 AMP - MULTI POSITION 1/2" STUDS 200 Amp Main c/w Blank Compartment

CATALOGUE #	TYPE	DESCRIPTION	DIMENSIONS (IN.)			WEIGHT
			H	W	D	
MSC22R	U/G	2 gang, c/w 1/2" compression studs	15 1/8	26 3/16	5 1/8	53 lbs.
MSC23R	U/G	3 gang, c/w 1/2" compression studs	15 1/8	34 15/16	5 1/8	70 lbs.
MSC24R	U/G	4 gang, c/w 1/2" compression studs	15 1/8	43 11/16	5 1/8	88 lbs.

- Factory Bussed 200 Amp Mains
- 200 Amp, 600 VOLT per position
- 2 - 4 position horizontal
- 4 Jaw meter sockets
- CSA weatherproof enclosure 3R
- Approved conductor range
- Line - studs (two 1/2" per phase)
- Provided for compression type wire connectors
- Load - #6 - 250 MCM CU/AL

- *Underground ONLY*
- Use **SXC022** for water heater lug kit
- Add suffix "H" for right hand entry

KNOCKOUT CODE	CONDUIT SIZE
G	1 1/4", 1 1/2", 2", 2 1/2"
AA	1/2"
F	1 1/4", 1 1/2", 2", 2 1/2", 3"

