## SATCO NUVO

Project Name

Location

Prepared By



## **SATCO S8020**

24FT/LED/STRING LIGHT/120V

Notes

General	
Status	Active
Finish	Black
Wattage	12
Style	Industrial
CCT (Kelvin)	2700
Color Temperature	Warm White
Length (in.)	288

Specifications	
Technology	LED
CRI	80
Lumen Output	100
Rated Hours	15000
Voltage	120V
Dimmable	Non-Dimmable
Glass Description	Clear
Weight (lb.)	3.33
Fixture Material	PVC
Recommended Dimmer	N/A
Fixture Type	String Light

Wire Length	24 in.
Compliance	
Safety Listing	cETLus
Location Rating	Wet
Energy Star	No
CA Prop 65	Lead
RoHS Compliant	Yes

Additional Information		
Includes	12 1-Watt LED Filament Bulbs; Satco part S8021	
Installation Notes	Connect up to 30 units.	
Warranty	3 Year Limited - 10 hr per day	









Dimensions