



Product Specifications

TLGU-19

Description

Line voltage track head cylinder for use with GU-10 50W bulbs.

- Directional light source providing 90° vertical aiming capability with 340° horizontal rotation
- Re-lamps from the front
- Dimmer compatible
- Lead wires concealed within stem
- Porcelain 120V AC GU-10 base socket

| Available Finishes | Model # |
|--------------------|-------------|
| Satin Nickel | TLGU-19-SN |
| Oil Rubbed Bronze | TLGU-19-ORB |
| White | TLGU-19-WH |

Lamp:

GU-10 base halogen 50W (max.)

Not Included

120V AC 60Hz

KENDAL LIGHTING INC.

Vancouver Office / Warehouse / Showroom

#110, 6780 Dennett Place, Delta, BC V4G 1N4
Ph: (604)952-5510 • Toll Free: 1-888-306-FANS (3267)
Fax: (604)952-5513 • Toll Free: 1-888-561-8722

Toronto Office / Warehouse / Showroom

#Unit 1, 3500 Laird Road, Mississauga, Ontario L5L 5Y4
Ph: (905)607-4004 • Toll Free: 1-866-221-5335
Fax: (905)607-4664 • Toll Free: 1-866-844-8406

Edmonton Office / Warehouse

16650 - 114 Avenue, Edmonton, Alberta T5M 3R8
Ph: (780)455-5500 • Toll Free: 1-877-455-5597
Fax: (780)452-1706

Dallas Showroom

Dallas Market Center
2100 Stemmons Freeway, Ste. 4739
Dallas, Texas 75207

Project: _____

Fixture Type: _____

Location: _____

Contact / Phone: _____

