

Ordering information

TrueForce MasterClass LED high-bay (Type B)



Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Replace Watts (W)	Lumens (lm)	Beam angle	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	
TrueForce MasterClass EX39 lamps										
D	557231	929002282604	145HB/LED/840/ND NB DL BB 4/1	145	250-400	20,000	Narrow	80	4000	50,000
D	557264	929002282804	145HB/LED/840/ND WB UDL BB 4/1	145	250-400	20,000	Wide	80	4000	50,000
D	557256	929002282904	145HB/LED/850/ND NB DL BB 4/1	145	250-400	20,000	Narrow	80	5000	50,000
D	557280	929002283104	145HB/LED/850/ND WB UDL BB 4/1	145	250-400	20,000	Wide	80	5000	50,000
D	557298	929002283204	165HB/LED/840/ND NB DL BB 4/1	165	400-600	25,000	Narrow	80	4000	50,000
D	557314	929002283404	165HB/LED/840/ND WB UDL BB 4/1	165	400-600	25,000	Wide	80	4000	50,000
D	557322	929002283504	165HB/LED/850/ND NB DL BB 4/1	165	400-600	25,000	Narrow	80	5000	50,000
D	557348	929002283704	165HB/LED/850/ND WB UDL BB 4/1	165	400-600	25,000	Wide	80	5000	50,000



EX39
145/165W

TrueForce MasterClass LED high-bay (Type A)



Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Replace Watts (W)	Lumens (lm)	Beam angle	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	
TrueForce MasterClass EX39 lamps										
	46560-9	929001264804	165HB/LED/740/ND NB DL 2/1	105	250	12,000	Narrow	70	4000	50,000
	46562-5	929001265004	165HB/LED/740/ND WB DL 2/1	105	250	12,000	Wide	70	4000	50,000
	46565-8	929001265304	165HB/LED/840/ND NB UDL 2/1	105	250	12,000	Narrow	80	4000	50,000
	46567-4	929001265504	165HB/LED/840/ND WB UDL 2/1	105	250	12,000	Wide	80	4000	50,000
	46560-9	929001264804	165HB/LED/740/ND NB DL 2/1	165	400	20,000	Narrow	70	4000	50,000
	46562-5	929001265004	165HB/LED/740/ND WB DL 2/1	165	400	20,000	Wide	70	4000	50,000
	46565-8	929001265304	165HB/LED/840/ND NB UDL 2/1	165	400	20,000	Narrow	80	4000	50,000
	46567-4	929001265504	165HB/LED/840/ND WB UDL 2/1	165	400	20,000	Wide	80	4000	50,000



EX39
105/165W

CorePro LED corn cobs



Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Replace Watts (W)	Lumens (lm)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	
CorePro E26 lamps									
D E	559633	929002395204	18CC/LED/830/ND E26 G2 BB 6/1	18	50-70	2300	80	3000	50,000
D E	559641	929002395304	18CC/LED/840/ND E26 G2 BB 6/1	18	50-70	2400	80	4000	50,000
D E	559658	929002395404	18CC/LED/850/ND E26 G2 BB 6/1	18	50-70	2500	80	5000	50,000
D E	559666	929002395504	27CC/LED/830/ND E26 G2 BB 6/1	27	70-100	3500	80	3000	50,000
D E	559674	929002395604	27CC/LED/840/ND E26 G2 BB 6/1	27	70-100	3700	80	4000	50,000
D E	559682	929002395704	27CC/LED/850/ND E26 G2 BB 6/1	27	70-100	3800	80	5000	50,000
D E	559690	929002395804	36CC/LED/830/ND E26 G2 BB 6/1	36	100-150	5000	80	3000	50,000
D E	559708	929002395904	36CC/LED/840/ND E26 G2 BB 6/1	36	100-150	5200	80	4000	50,000
D E	559716	929002396004	36CC/LED/850/ND E26 G2 BB 6/1	36	100-150	5400	80	5000	50,000
CorePro EX39 lamps									
D E	559724	929002396104	36CC/LED/830/ND EX39 G2 BB 6/1	36	100-150	5000	80	3000	50,000
D E	559732	929002396204	36CC/LED/840/ND EX39 G2 BB 6/1	36	100-150	5200	80	4000	50,000
D E	559740	929002396304	36CC/LED/850/ND EX39 G2 BB 6/1	36	100-150	5400	80	5000	50,000
D E	559757	929002396404	45CC/LED/830/ND EX39 G2 BB 6/1	45	150-175	6200	80	3000	50,000
D E	559765	929002396504	45CC/LED/840/ND EX39 G2 BB 6/1	45	150-175	6500	80	4000	50,000
D E	559773	929002396604	45CC/LED/850/ND EX39 G2 BB 6/1	45	150-175	6700	80	5000	50,000
D E	559781	929002396704	54CC/LED/830/ND EX39 G2 BB 6/1	54	150-250	7500	80	3000	50,000
D E	559799	929002396804	54CC/LED/840/ND EX39 G2 BB 6/1	54	150-250	7800	80	4000	50,000
D E	559807	929002396904	54CC/LED/850/ND EX39 G2 BB 6/1	54	150-250	8000	80	5000	50,000
D E	559815	929002397004	63CC/LED/830/ND EX39 G2 BB 6/1	63	175-250	8600	80	3000	50,000
D E	559823	929002397104	63CC/LED/840/ND EX39 G2 BB 6/1	63	175-250	9000	80	4000	50,000
D E	559831	929002397204	63CC/LED/850/ND EX39 G2 BB 6/1	63	175-250	9200	80	5000	50,000



E26
18W

E26
27W

E26
36W



EX39
36W

EX39
45W

EX39
54/63W

1. Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed. Warranty is based off of 15,000 hour claim. Lamps rated at 25,000 hours is for an unenclosed fixture. Life rating is 15,000 hours for enclosed. Warranty is based off of 25,000 hour claim.

D = Damp location E = Suitable for enclosed fixtures

TrueForce MasterClass LED corn cobs



Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Replace Watts (W)	Lumens (lm)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)
MasterClass EX39 lamps								
559849	929002397304	80CC/LED/840/ND EX39 G2 BB 3/1	80	175-250	12000	80	4000	50,000
559856	929002397404	80CC/LED/850/ND EX39 G2 BB 3/1	80	175-250	12000	80	5000	50,000
559864	929002397504	115CC/LED/840/ND EX39 G2 BB 3/1	115	250-400	18000	80	4000	50,000
559872	929002397604	115CC/LED/850/ND EX39 G2 BB 3/1	115	250-400	18000	80	5000	50,000
559880	929002397704	150CC/LED/840/ND EX39 G2 BB 3/1	150	320-400	24000	80	4000	50,000
559898	929002397804	150CC/LED/850/ND EX39 G2 BB 3/1	150	320-400	24000	80	5000	50,000



TrueForce MasterClass LED post top



Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Replace Watts (W)	Lumens (lm)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)
TrueForce MasterClass E39 lamps								
47359-5	9290013964	26ED23.5/LED/727/ND 120-277V G2 4/1	26	70	2800	70	2700	50,000
47357-9	9290013962	26ED23.5/LED/730/ND 120-277V G2 4/1	26	70	3000	70	3000	50,000
47358-7	9290013963	26ED23.5/LED/740/ND 120-277V G2 4/1	26	70	3000	70	4000	50,000
47362-9	9290013967	35ED23.5/LED/727/ND 120-277V G2 4/1	35	100	5000	70	2700	50,000
47360-3	9290013965	35ED23.5/LED/730/ND 120-277V G2 4/1	35	100	5000	70	3000	50,000
47361-1	9290013966	35ED23.5/LED/740/ND 120-277V G2 4/1	35	100	5000	70	4000	50,000
47355-3	9290013960	38ED28/LED/727/ND 120-277V G2 CT 4/1	38	100	5000	70	2700	50,000
47604-4	9290018184	38ED28/LED/730/ND 120-277V G2 CT 4/1	38	100	5000	70	3000	50,000
47605-1	9290018185	38ED28/LED/740/ND 120-277V G2 CT 4/1	38	100	5000	70	4000	50,000
47365-2	9290013970	55ED28/LED/727/ND 120-277V G2 4/1	55	150	8000	70	2700	50,000
47363-7	9290013968	55ED28/LED/730/ND 120-277V G2 4/1	55	150	8000	70	3000	50,000
47364-5	9290013969	55ED28/LED/740/ND 120-277V G2 4/1	55	150	8000	70	4000	50,000



CorePro LED high-bay/low-bay



Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Replace Watts (W)	Lumens (lm)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)
CorePro E26 lamps (120V)								
541912	929001989604	25HB/LED/830/ND FB 6/1	25	40	2650	80	2700	25,000
541920	929001989704	38HB/LED/830/ND FB 6/1	38	55	3500	80	3000	25,000
541938	929001989804	45HB/LED/830/ND FB 6/1	45	70	4500	80	4000	25,000
541950	929001990004	25HB/LED/850/ND FB 6/1	25	40	2800	80	2700	25,000
541960	929001990104	38HB/LED/850/ND FB 6/1	38	55	3800	80	3000	25,000
541978	929001990204	45HB/LED/850/ND FB 6/1	45	70	4800	80	4000	25,000
543066	929001999104	25HB/LED/840/ND FB 6/1	25	40	2800	80	2700	25,000
543074	929001999204	38HB/LED/840/ND FB 6/1	38	55	3800	80	3000	25,000
543082	929001999304	45HB/LED/840/ND FB 6/1	45	70	4800	80	4000	25,000
CorePro EX39 lamps (120-277V)								
542290	929001990304	65HB/LED/850/ND FB 4/1	65	125	7000	80	2700	25,000
542316	929001990504	75HB/LED/850/ND FB 4/1	75	150	8500	80	3000	25,000
542308	929001993004	65HB/LED/840/ND FB 4/1	65	125	7000	80	4000	25,000
542324	929001993104	75HB/LED/840/ND FB 4/1	75	150	8500	80	4000	25,000



CorePro LED wall packs



Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Replace Watts (W)	Lumens (lm)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)
Wall Pack E26 lamps (100-277V)								
559906	929002397904	20WP/LED/830/ND E26 G2 BB 6/1	20	70-100	2800	80	2800	50,000
559914	929002398004	20WP/LED/840/ND E26 G2 BB 6/1	20	70-100	2900	80	2900	50,000
559922	929002398104	20WP/LED/850/ND E26 G2 BB 6/1	20	70-100	3000	80	3000	50,000
Wall Pack EX39 lamps (100-277V)								
559930	929002398204	40WP/LED/840/ND EX39 G2 BB 6/1	40	100-175	5800	80	5800	50,000
559948	929002398304	40WP/LED/850/ND EX39 G2 BB 6/1	40	100-175	6000	80	6000	50,000
559962	929002398404	60WP/LED/840/ND EX39 G2 BB 6/1	60	175-250	8700	80	8700	50,000
559954	929002398504	60WP/LED/850/ND EX39 G2 BB 6/1	60	175-250	9000	80	9000	50,000

