



Design Series

STANDARD is proud to introduce its new DESIGN Series of LED lamps, focusing on providing LED lamps that offer good balance between great performance and aesthetic conception. These products mimic the look of the traditional lamps, while offering all of the benefits of LED technology.

LED Lamp



G9



GU10



PAR20

Order code	Description	Watts (W)	Base	Volts (VAC)	Color temp. (K)	CRI	Life L70 (hrs)	Lumen output (lm)	Beam angle (°)	CBCP (cd)	Traditional equivalent (W)	Case qty (inner/master)
G9												
67095 ¹	G9/2.7W/27K/CL/DESIGN/STD	2.7	G9	120	2 700	80	15 000	320	360	-	35	100/1 000
67096 ¹	G9/2.7W/30K/CL/DESIGN/STD	2.7	G9	120	3 000	80	15 000	320	360	-	35	100/1 000
67097 ¹	G9/2.7W/40K/CL/DESIGN/STD	2.7	G9	120	4 000	80	15 000	320	360	-	35	100/1 000
GU10												
67615 ²	GU10/7W/30K/45/DESIGN/STD	7	GU10	120	3 000	80	25 000	530	45	600	50	10/100
67616 ²	GU10/7W/40K/45/DESIGN/STD	7	GU10	120	4 000	80	25 000	530	45	600	50	10/100
PAR20												
67607	P20/7W/30K/45/DESIGN/STD	7	E26	120	2 700	80	25 000	500	45	520	50	10/60
67608	P20/7W/40K/45/DESIGN/STD	7	E26	120	3 000	80	25 000	500	45	520	50	10/60



Order code	Description	Watts (W)	Base	Volts (VAC)	Color temp. (K)	CRI	Life L70 (hrs)	Lumen output (lm)	Beam angle (°)	CBCP (cd)	Traditional equivalent (W)	Case qty (inner/master)
PAR30SN												
67609	P30S/10W/30K/45/DESIGN/STD	10	E26	120	3 000	80	25 000	750	45	810	60	1/20
67610	P30S/10W/40K/45/DESIGN/STD	10	E26	120	4 000	80	25 000	750	45	810	60	1/20
PAR30LN												
67611	P30L/13W/30K/45/DESIGN/STD	13	E26	120	3 000	80	25 000	950	45	1 100	75	1/20
67612	P30L/13W/40K/45/DESIGN/STD	13	E26	120	4 000	80	25 000	950	45	1 150	75	1/20
PAR38												
67613	P38/15W/30K/45/DESIGN/STD	15	E26	120	3 000	80	25 000	1 200	45	1 150	100	1/10
67614	P38/15W/40K/45/DESIGN/STD	15	E26	120	4 000	80	25 000	1 200	45	1 500	100	1/10



Lumen values are derived from photometric testing. For a complete list of compatible dimmers and ENERGY STAR qualified products, please visit www.standardpro.com