SATCO' NUVO

Project Name

Location

Prepared By



SATCO S39752

60W/LED/HID/MB-G3/50K/100-277V

Notes


General Status Active Watts 60 Incandescent Equivalent 500 Fluorescent Equivalent 85 HID Equivalent 250 Volts 100V-277V Shape Corncob Base Mogul Extended ANSI Base EX39 Finish Clear CCT (Kelvin) 5000 Temperature Natural Light CRI 80 Lumens 8400 Beam Spread 120;150;260 Dimmable Non-Dimmable Hours Rated 50000 Lamp Type LED HID LED Technology Width: 9.30 in. Depth: 9.30 in. Min Compartment Size Height: 9.80 in. Electrical

Liectrical	
Operating Frequency	50/60 Hz
Power Factor	>0.9
Surge Protection	Built-in surge protection - 4KV
THD	<20%
Operating Temperature	-20C (-4F) to a maximum of +65C (+149F)

Physical MOL 7.76 MOD 4.13 Housing Color White Photocell Optional Add-On Weight (lb.) 2.05

Additional Info	PIR Sensor available as an accessory
Rated For Enclosed Fixture	Yes
IP Rating	IP64
Specification Note	Closed 260 deg; Partial 150 deg; Open 120 deg
Warranty	5 Year Limited - Hi-Pro
Compliance	
Safety Listing	cULus Classified
Location Rating	Damp
Energy Star	No

For More Information Visit: <u>https://www.satco.com/</u>



in f V 9

DLC Approved	Yes
DLC ID	PL1DH99JBHHE
CEC Status	Lawful for sale in California
RoHS Compliant	Yes
SDS Sheet	LED_Lamp

Copyright 2020 Satco Products, Inc. All Rights Reserved

For More Information Visit: <u>https://www.satco.com/</u>

