## SATCO" NUVO

Project Name



## NUVO 65-672

60W FULL CUTOFF WALL PACK

Notes

General Status Active Fixture Type Wall Pack Finish Bronze Wattage 60 Lumen Output 7200L - 7500L CCT (Kelvin) 3000K/4000K/5000K **IP** Rating IP65 Indoor or Outdoor Fixture Outdoor Specifications Technology LED CRI 80 Voltage 120V-277V Beam Angle 90x100 Rated Hours 50000 -40C (-40F) to a maximum of +40C **Operating Temperature** (+104F) Dimmable 1-10V Dimming Only Lens Material Impact Resistant PC Surge Protection Built-in surge protection - 4KV 5.07 Weight (lb.) Material Die-Cast Aluminum Dimensions Height (in.) 5.10 12.61 Width (in.) Extension (in.) 6.86 Compliance Safety Listing cULus Location Rating Wet Energy Star No **DLC Approved** Yes PLXV561HFHT2 DLC ID **RoHS** Compliant

## Additional Information

FCC Compliant

Warranty

5 Year Limited - Fixtures

Yes

Yes

For More Information Visit: https://www.satco.com/

