

Project Name

Location

Prepared By



Notes

[www] 11-09-2020 01:10:21

General

Status	Active
Fixture Type	Wall Pack
Finish	Bronze
Wattage	80
Lumen Output	9600L - 10000L
CCT (Kelvin)	3000K/4000K/5000K
IP Rating	IP65
Indoor or Outdoor Fixture	Outdoor

Specifications

Technology	LED
CRI	80
Voltage	120V-277V
Beam Angle	90x100
Rated Hours	50000
Operating Temperature	-40C (-40F) to a maximum of +40C (+104F)
Dimmable	1-10V Dimming Only
Lens Material	Impact Resistant PC
Surge Protection	Built-in surge protection - 4KV
Weight (lb.)	5.73
Material	Die-Cast Aluminum

Dimensions

Height (in.)	5.10
Width (in.)	12.61
Extension (in.)	6.86

Compliance

Safety Listing	cULus
Location Rating	Wet
Energy Star	No
DLC Approved	Yes
DLC ID	PLN9FQOJ5TZA
CEC Status	Lawful for sale in California
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------