## SATCO NUVO

Project Name

Location Prepared By



	•			•
11" ACR	YLIC LE	ED FLUS	SH FIXT	URE

Notes	
-------	--

General	
Status	Active
Finish	White
Wattage	16
CCT (Kelvin)	3000K/4000K/5000K
Width (in.)	11.54
Height (in.)	3.04
Indoor or Outdoor Fixture	Indoor

Specifications	
Technology	LED
CRI	90
Lumen Output	990L - 1100L
Rated Hours	50000
Voltage	120V
Dimmable	Yes-Dimmable
Recommended Dimmer	Triac
Weight (lb.)	1.21
Fixture Material	Acrylic
Fixture Type	Flush Mount
Operating Temperature	-20C (-4F) to a maximum of +40C (+104F)

Compliance	
Safety Listing	cETLus
Location Rating	Damp
Energy Star	Pending
CEC Status	Lawful for sale in California
RoHS Compliant	Yes
FCC Compliant	Yes

A		- 1 1 6		
A(6(6	mon	ai ini	orma	пю

Warranty 5 Year Limited - Fixtures







